eDrive™ Nitro

NORTHROP GRUMMAN

ED4U SERIES DRIVER LASER SYSTEM & LASER DIODE DRIVER

FEATURES AND BENEFITS



- Operates in either CW or QCW modes
 - 0-350V compliance voltage range
- Water or Air cooled versions available
 - CE marked version available
 - Integrated power supply (optional)
 - Integrated RF driver (optional)
 - 19" rack mountable
 - Labview compatible* RS232 and RS485

With all of the standard drive specifications of the eDrive™, the eDrive Nitro integrates optional power supplies, RF drivers, and other accessories in a single rack-mounted housing. Configurable for driving diodes in either CW or QCW operating modes, all aspects of your laser system can be managed with one unit. The eDrive Nitro is equipped with multiple control options, an easy to use local front panel interface along with a host of digital remote control options, including Labview* compatibility, which are all offered as standard.

The eDrive Nitro has been designed to maximize reliablilty. All system components are conservatively rated. High power circuits are physically separated from low power circuits. Minimal internal interconnect wiring increases reliability. A variety of power supplies, single or dual-axis Q-switch drivers/controllers, and temperature controller options are available. Please contact us for more information.


^{*}Labview[™] is the property of National Instruments Corporation.


eDrive™ Nitro

SPECIFICATIONS

	Air Cooled		Water Cooled	
Amplitude:	CW	QCW	CW	QCW
Output Current	0-50 A	0-300 A **	0-70 A	0-300 A **
Display Resolution	100 mA	100 mA	100 mA	100 mA
Accuracy	± 2%	± 2%	± 2%	± 2%
Noise	< 50 mA p-p	< 50 mA p-p	< 50 mA p-p	< 50 mA p-p
*See chart on page 3 for duty				
Pulse Rate:	CW	QCW	CW	QCW
Range	_	0 - 50 kHz	_	0 - 50 kHz
Display Resolution (1 Hz)	_	0 - 100 Hz	_	0 - 100 Hz
(10 Hz)	_	100 Hz - 1 kHz	_	100 Hz - 1 kHz
(100 Hz)	_	1 kHz - 50 kHz	_	1 kHz - 50 kHz
Accuracy	_	<u>+</u> 2%	_	<u>+</u> 2%
Pulse Width:	CW	QCW	CW	QCW
Range	_	10 μs - 100 ms	_	10 μs - 100 ms
Display Resolution	_	100 ns	_	100 ns
T W T		5 μs Typical (100 A)		5 μs Typical (100 A)
Transition Time	_	40 µs Typical (300 A)	_	40 μs Typical (300 A)
Trigger In:	CW	QCW	CW	QCW
Type		Positive Edge Trigger	_	Positive Edge Trigger
Signal Input	_	TTL or 5 V CMOS		TTL or 5 V CMOS
Minimum Width	_	50 μs	_	50 μs
	_	50 μs	_	50 μs
Input Impedance	_	50 72	_	50.72
Trigger Out:	CW	QCW	CW	QCW
Туре	_	User configurable for EO Q-switched operation	_	User configurable for EO Q-switched operation
Characteristics	_	TTL of 5V CMOS	_	TTL of 5V CMOS
Compliance Voltage:	CW	QCW	CW	QCW
Range	0 - 350 V	0 - 350 V	0 - 350 V	0 - 350 V
Display Resolution	0.1 V	0.1 V	0.1 V	0.1 V
Accuracy	<u>+</u> 2%	<u>+</u> 2%	<u>+</u> 2%	<u>+</u> 2%
,	_	_	_	_
Current Monitor:	CW	QCW	CW	QCW
Туре	10 A/V 0-5 V	20 A/V 0-5 V (0-15 V for	10 A/V 0-7 V	20 A/V 0-5 V (0-15 V for
Accuracy	<u>+</u> 2%	high current models) ± 2%	<u>+</u> 2%	high current models) ± 2%
Interlocks:	CW	QCW	cw	QCW
Open Circuit Voltage	5 VDC nominal	5 VDC nominal	5 VDC nominal	5 VDC nominal
Short Circuit Current	1 mA nominal	1 mA nominal	1 mA nominal	1 mA nominal
Short Circuit Current				
_	Switch contact closure	Switch contact closure	Switch contact closure	Switch contact closure
Туре	or TTL or 5 V CMOS	or TTL or 5 V CMOS	or TTL or 5 V CMOS	or TTL or 5 V CMOS
	compatible	compatible	compatible	compatible
General:	CW	QCW	CW	QCW
Operating Temperature	0 - 40°C, non condensing	0 - 40°C, non condensing	0 - 40°C, non condensing	0 - 40°C, non condensing
	100 - 240 VAC, 50/60 Hz,	100 - 240 VAC, 50/60 Hz,	100 - 240 VAC, 50/60 Hz,	100 - 240 VAC, 50/60 Hz,
Power Input	15A max	15A max	15A max	15A max


DUTY CYCLE RATINGS





eDrive™ Nitro

MECHANICAL DRAWINGS



Copyright © 2010 Northrop Grumman Cutting Edge Optronics All Rights Reserved. Northrop Grumman Cutting Edge Optronics reserves the right to change product design and specifications at any time without notice. No license is granted by implication or otherwise under any patents or patent rights of Northrop Grumman Cutting Edge Optronics or others. No responsibility is assumed for the use of these products, nor for any infringement on the rights of others resulting from the use of these products. Information contained herein is believed to be reliable and accurate.

